



ARUNTM

AN ISO 9001 : 2008 CERTIFIED COMPANY



CTN 110D - 150D
Two|For|One|Twister
FOR COTTON / SPUN YARN

Cradle

The cradle is designed such that it can be adjusted to hold take up packages of different taper angles.

Cradle tension device maintains constant contact pressure throughout the complete take up process.




Auto cradle - lifting device (Optional)

In case of yarn breakage or when the supply package is finished the cradle will be lifted automatically.

Tension Device and Tension device holder

Easy setting capsule type tension device is provided for smooth yarn path. Tension device holder is provided on spindle mounting channel to hold the tension device during doffing, to keep the floor area clean.



Dropper

In case of yarn breakage, the supply of thread will be stopped by the action of dropper and at the same time cradle lifting device will come into action.



Take up package

High precision cam in the gearbox gives perfect package build even at high speed.



Control Panel

Slow start by Star - Delta panel with rpm, tpm, yarn speed display, ammeter and S&Z Switch.

Main Features


- High quality for fine and coarse counts
- High productivity and efficiency
- Low power consumption and maintenance
- Dynamically balanced spindle with high grade hardened steel
- Overfeed roller with stainless steel and ceramic guides
- Gearbox in oil bath
- Slow start by Star - Delta panel with rpm, tpm, yarn display, ammeter and S&Z Switch

Spindle & Bolster

ARUN manufactures high quality spindles and bolsters which exhibit excellent dynamic balance and durability even while operating at high speeds.

Overfeed

The required take up package density is precisely controlled by overfeed roller, which is provided with stainless steel discs and ceramic guides.



Free Ballooning

ARUN adopts the Free Ballooning system to retain the yarn quality without damaging the yarn.

Anti - patterning device

Built in the gear box, this device prevents patterning of the yarn on the take up package.

Aluminum Pot (Anodized)


Different sizes & shapes of pots are available for various yarn counts to meet the different requirements of customers.



Gearbox (in oil bath)

Heavy and sturdily designed gearbox with anti pattern device and cam mechanism manufactured with graded casting & operating in oil bath gives life time performance. Thus it gives perfect package build even at high speed with low maintenance.


Front positioning of the change gear train makes the changing of gears simple in case of altering the TPM and S / Z orientation.



TECHNICAL SPECIFICATIONS

| | |
|---|--|
| Pot diameter | 110 / 120 / 140 / 150 mm |
| Max. Take up Package Weight | Up to 2 kg |
| Twist range | 6 to 50 TPI |
| Count range | 2/10 to 2/120 Ne |
| Spindle gauge | 210 mm |
| Feed Package / Supply Package | |
| Max. Length | 170 mm |
| Weight | Up to 600 gm |
| Traverse Length | 152 mm |
| Delivery Package / Take up Package | |
| Max. Length | 170 mm |
| Max. Weight | Up to 2 kg |
| Conicity | 3° 30" / 4° 20" / 5° 57" |
| Traverse | 152 mm |
| Max. Spindle speed mechanical | 12000 rpm |
| Spindle drive | Tangential |
| Tension Device | Capsule type Tension Device |
| Panel | Slow Start By Star - Delta Panel With rpm, tpm, Yarn Speed Display Meter, Ammeter, S & Z Switch |

OVER ALL DIMENSIONS AND INSTALLATION DIAGRAM



| NO. OF SPINDLES | NO. OF SECTIONS | MACHINE DIMENSIONS | | | MOTOR | | |
|-----------------|-----------------|--------------------|------------|-------------|--------------|----------|-----|
| | | LENGTH (ft) | WIDTH (ft) | HEIGHT (ft) | 110/120 (hp) | 140 (hp) | NOS |
| 240 | 10 | 53' | 3' | 6' 2" | 5 | 7.5 | 2 |
| 264 | 11 | 57' 6" | 3' | 6' 2" | 5 | 7.5 | 2 |
| 288 | 12 | 62' | 3' | 6' 2" | 7.5 | 10 | 2 |
| 312 | 13 | 66' 6" | 3' | 6' 2" | 7.5 | 10 | 2 |
| 336 | 14 | 71' | 3' | 6' 2" | 10 | 12.5 | 2 |
| 360 | 15 | 75' 6" | 3' | 6' 2" | 10 | 12.5 | 2 |

Motor capacity depends on spindle speed, yarn count and twist range.


ARUNTM
 TEXTILE ENGINEERS PVT. LTD.
Reliable Partners In Progress

45, Jasukaka Wadi, Opp. Leprosy Hospital, A.k. Road, Surat-395008. (Gujarat) INDIA.

Tel. +91-261-2552222, 2550061 Fax: +91-261-2551836

Website : www.aruntexeng.com Email : info@aruntexeng.com

*Technical specifications are subject to change without specific prior notice due to continuous development